

0.	Detailed Specification of the Stores	Quantity
	<p><b>Low Speed Diamond Wheel Saw:</b>            Model 650 or similar Low Speed Diamond Wheel Saw            with everything necessary to operate including at least the following</p> <ul style="list-style-type: none"> <li>Single Axis Goniometer</li> <li>Double Clamp Holder</li> <li>Diamond Wheel</li> <li>Abrasive Wheel (Aluminum Oxide, 4" diameter)</li> <li>Abrasive Wheel (Silicon Carbide, 3" diameter)</li> <li>Water soluble coolant, 1 quart</li> <li>Silicon Carbide Dressing Stick</li> <li>Mounting Wax Samples - Includes MWH 135, MWH 080, MWM 070, and MWS 0</li> <li>Cutting weight, 200 grams</li> <li>Cutting weight, 100 grams (mounted on unit)</li> <li>Allen wrench set, 1/16 thru 3/16</li> <li>Specimen mounting plate kit #1</li> <li>Plastic Splash Guard</li> <li>2.40" Support Collars (qty 2)</li> <li>1.87" Support Collars (qty 2)</li> <li>1.37" Support Collars (qty 2)</li> <li>O-Ring, 1.484 ID x 1.762 OD x .139 thk (qty 2)</li> <li>Spacer, wheel, .75" (mounted on unit)</li> <li>Lock, work table (mounted on unit)</li> <li>Lock, blade holder (mounted on unit)</li> </ul>	01